

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #2007711-1
IMP100S,R,RA3P16C,UG,39



TE Part #2187308-1
Tin Man Recept Assy 4 Pair 16 Column



TE Part #2198235-3
SFP+ Enhanced 1x6, Networking Heatsink



TE Part #2204155-8
MBXL R/A HDR 7P+40S




TE Part #2227104-1
1X2 CAGE ASSY, BHND BEZEL, QSPF28




TE Part #6368062-8
2X4 OFFSET STK MJ,SHLD,W/LED




TE Part #6368116-4
2X6 OFFSET STK MJ,W/RIGHT GN LED



TE Part #6368168-7
2X1 OFFSET ST/JK,LED(G&Y)12PNL



TE Part #6450570-9
MBXL R/A RCPT 1P+16S+1P



TE Part #1370495-1
.050 CL FFC,30P DBL CABLE ASSY

Documents

Product Drawings

IMP,PWR,3PR,HDR,R-HLD,2X,797-2,797-9

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-2180851-8_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2180851-8_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2180851-8_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English

Agency Approvals

UL

English