



Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Plug to Plug Relay Header**

Mating Retention: **With**

Mating Retention Type: **Locking Latch**

Connector System: **Wire-to-Panel**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Plug to Plug Relay Header
Connector System	Wire-to-Panel
Sealable	No

Configuration Features

Number of Positions	18
Number of Rows	1

Electrical Characteristics

Operating Voltage	50 VAC
-------------------	--------

Body Features

Primary Product Color	White
-----------------------	-------

Contact Features

Contact Base Material	Brass
-----------------------	-------



Contact Type	Pin
Contact Retention Within Housing	Without
Contact Current Rating (Max)	2 A

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	With
Panel Mount Feature Type	Latches
Mating Retention	With
Mating Retention Type	Locking Latch
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Nylon 66
Centerline (Pitch)	1.5 mm[.059 in]

Dimensions

Panel Thickness (Recommended)	.81 – 1.6 mm[.032 – .063 in]
Connector Height	11.8 mm[.464 in]
Connector Length	35.1 mm[1.381 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	UL
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	600
Packaging Method	Bag & Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM7053-H8172
Mini Common Termination (CT) Housings



TE Part # 1-353293-8
MINI CT MT REC ASSY 18P GRAY



TE Part # CAT-AM7053-C7671
Mini Common Termination Contacts



TE Part # 6-353293-8
MINI CT MT REC ASSY 18P BLUR



TE Part # 1-353293-3
MINI CT MT REC ASSY 13P GRAY

Also in the Series | AMP Mini CT



Connector Contacts(4)



Connector Hardware(10)



PCB Headers & Receptacles(332)



Rectangular Connector Housings(38)



Rectangular Power Connectors(76)



Standard Rectangular Connectors(172)



Wire-to-Board Connector Assemblies & Housings(114)




Wire-to-Board Headers & Receptacles (332)


Customers Also Bought



TE Part #292215-3
MINI CT SGL RELAY 3P NAT



TE Part #6-292233-0
1.5 MINI CT DRAWER 60P PLUG



TE Part #6-292235-0
1.5 MINI CT DRAWER 60P REC



TE Part #292254-4
CT RELAY HDR ASSY 4P NAT




TE Part #292254-5
CT RELAY HDR ASSY 5P NAT




TE Part #2-353293-7
1.5MM CT MT REC ASS'Y 7P BLACK




TE Part #1-353908-8
CT REC HSG 18P CRIMP TYPE WHIT



TE Part #1-1123919-4
1.5 MINI CT DUST COVER



TE Part #8-292155-3
SGL HDR PANEL MOUNT ASSY



TE Part #8-292155-4
SGL HDR PANEL MOUNT ASSY

Documents



Product Drawings

MINI CT SGL RELAY 18P NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-292215-8_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-292215-8_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-292215-8_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Workmanship Specification

English