


OZ-SS-109LM1F,000 ☑ SUPERSEDED

TE Internal #: 1461868-7

TE Internal Description: OZ-SS-109LM1F,000

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #1-640453-4
14P MTA100 HDR ASSY SQ R/A



TE Part #8-1717011-4
EP CONN.HDR ASSY 4/5P BLACK
(NO.3 POST)



TE Part #1721083-5
OJ-SS-109LMHF,000




TE Part #3-1969453-1
HSG,RECP,POSI-LOCK&STD FAST250



TE Part #2238190-1
LOW PROFILE MINI AMP-IN SM



TE Part #2266067-1
OCEAN_2.0_Applicator-S-110F180F-
RSM




TE Part #3-2304525-3
3P DUOPLUG MK II



TE Part #1-2336231-6
Power Versa-Lock TNL CAP, 2X3 KEY A



TE Part #9-1440003-9
PCH-109D2,000



TE Part #CV08194001
VERSAFLEX-FR-UL-1/4-09-SP

Documents

Product Drawings

[OZ-SS-109LM1F,000](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1461868-7_G4.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1461868-7_G4.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1461868-7_G4.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



OZ_OZT Series Relay Data Sheet - English

English

Product Specifications

Definitions General Purpose Relays

English