1-63986-1 ✔ ACTIVE

FASTON | FASTON 250

TE Internal #: 1-63986-1

TE Internal Description: 250 FASTON,PCB TAB,BR

View on TE.com >



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-P360
P360 Pin Insertion Machine



TE Part # CAT-P550
Pin Insertion Machine P550




TE Part # 61368-1
250 FASTON REC 24-20 AWG TPBR



TE Part # CAT-P100
Pin Insertion Machine P100



TE Part # CAT-P280
P280 PIN INSERTION MACHINE



TE Part # 2410420-3
EP PIN INSERTION MACHINE




TE Part # CAT-P300
Pin Insertion Machine P300

Also in the Series | FASTON 250



Compression Connectors(4)




Crimp Terminal Housings(117)



Insertion & Extraction Tools(6)



Insulation Boots & Sleeves(16)



Magnet Wire Terminals(1)



PCB Terminals(131)



Quick Disconnects(404)



Splices(4)

Customers Also Bought



TE Part #1623929-3
CFR200 5% 10K



TE Part #1-1623929-4
CFR200 5% 18K



TE Part #2-1624235-3
ES 3WATT 100R 5% T/R



TE Part #2232043-5
5P, RAST 5 Tab Header, THV

Documents

Product Drawings

250 FASTON,PCB TAB,BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-63986-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-63986-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-63986-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

FASTON TERMINALS (INSULATED AND UNINSULATED) - FULL CATALOG

English

Product Specifications

Application Specification

English

Application Specification

English