
1735438-4 × OBSOLETE

TE Internal #: 1735438-4

TE Internal Description: MiniDIMM,R/A,1.5V,DDR3,STD,30Au/AuFl

View on TE.com >







Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Customers Also Bought



TE Part #6-534267-9
16 MODIV VRT DR DE 100/125



TE Part #7-534267-0
12 MODIV VRT DR DE 100/125



TE Part #1-1747981-1
Std HDMI, RA, SMT, Panel grd, Flange

TE Part #2314015-1
STRADDLE MOUNT QSFP28, 1X6, RECEPTACLE

TE Part #7-5177986-1
0.8FH,P07H.5,040,30/Sn,TR,SC



TE Part #6450361-1
MBXL R/A RCPT 24S+6P



TE Part #1367643-1
DWDM Cage Assembly, 11 PF

TE Part #2057548-3
SFP+ Stout 1X4 Cage Assembly, Press-Fit



TE Part #2169802-4
IMP,Power,4PR,R/A,Hdr,5.7,6.9Tin

TE Part #2331511-2
RCPT CONN R/A SMT 76 POSN QSFP-DD

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_1735438-4_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1735438-4_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1735438-4_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

DDR3 DIMM Sockets Flyer 6-1773454-7 05/09

English

6-1773457-3_DDR3_DIMM_SOCKETS

Product Specifications

Application Specification

English