
174047-1 ✔ ACTIVE

TE Internal #: 174047-1

TE Internal Description: 040 MLC PLUG HSG 20P NATURAL

View on TE.com >







Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 174977-1
040 MLC 20POS CAP ASSY V TIN


Customers Also Bought




TE Part #175180-1
040 MULTILOCK REC CONT PRE-TIN




TE Part #CAT-M8793-CH8172
MQS, CONNECTOR HOUSING



TE Part #927852-6
PL 250 REC TERMINAL 20-17 AWG PTPB




TE Part #963768-1
TAB 9.5x1.2 CONTACT CS SRC Sn




TE Part #1452187-1
1X10 GET ASSY, UNSLD FEM KEY A



TE Part #1897550-1
025/090 HYB 56P PLUG ASSY



TE Part #174931-1
070 MLC W-W CAP HSG 8P NATURAL



TE Part #936092-1
090III 10P PLUG ASSY



TE Part #1952074-2
.250 SRS, RECP HSG, 2P WITH SE

Documents

Product Drawings

040 MLC PLUG HSG 20P NATURAL

English

CAD Files

Customer View Model

ENG_CVM_CVM_174047-1_J.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_174047-1_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_174047-1_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Crimping .040 Series, Receptacle Contact

Japanese

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

English

040 SERIES MULTI-LOCK CONNECTOR

English

Agency Approvals

UL Report

English