



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FFC Connectors > 2.54mm FFC Connectors Receptacle Housing



FFC Connector Product Type: **Housing**

Connector System: **Wire-to-Board**

Number of Positions: **18**

Centerline (Pitch): **2.54 mm [.1 in]**

Number of Rows: **2**

[All 2.54mm FFC Connectors Receptacle Housing \(143\)](#)

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle
FFC Connector Product Type	Housing
Connector System	Wire-to-Board
Insertion Force Type	Normal

Configuration Features

Number of Positions	18
Number of Rows	2

Electrical Characteristics

Operating Voltage	300 VAC
Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	720 VAC

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Type	Socket
--------------	--------

Mechanical Attachment



Mating Alignment Type	Polarization
Mating Retention Type	Detent Window
Mating Retention	With
Mating Alignment	With
Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon GF
Centerline (Pitch)	2.54 mm[.1 in]
FFC Cable Entry	Straight

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-F439-P65127
FFC Connector Pin Contacts, 1.27 mm




TE Part # CAT-F439-S01339127
1.27mm FFC Connectors Socket Contacts



TE Part # 103169-8
20 MODII HDR DRST SHRD .100CL



TE Part # 494060-3
FFC TERMINAL PLT




TE Part # CAT-F439-S01339254
2.54mm FFC Connectors Socket Contacts



TE Part # 88189-4
018 HOUSING FFC PIN DR 100CL



TE Part # 1-487137-1
FFC SOLDER TAB FULL 100 SN



TE Part # 1761852-1
FFC RCPT 100SNPB RL NO LUBE




TE Part # CAT-F439-P65254
2.54mm FFC Connectors Pin Contacts




TE Part # 487843-1
FFC SPLICE CONTACT


Customers Also Bought




TE Part #120603-2
1FHR,84,30A/P,S,N,S11,12




TE Part #208972-2
CONNECTOR #2 PLUG




TE Part #1-448138-2
CNCT, SZ 20 PSTD PIN




TE Part #1218240-2
PIN CONT,SZ20,SC,FR,ARINC 600



TE Part #1883910-1
A600, SZ 3 RCPT 150/150/13C2/




TE Part #1738220-1
GPR SPANER WRENCH



TE Part #6-1542003-8
HTS630-P=HS ASSY CLIP



TE Part #1-86479-8
28 MODII HDR DRRA UNSHRD .100



TE Part #3-208972-0
NIC66H52A00AA0



TE Part #3-87230-5
70 MODII HDR DRRA UNSHRD .100

Documents

Product Drawings

018 HOUSING FFC RCPT DR 100CL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-88179-0_AZ_c-1-88179-0-az.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-88179-0_AZ_c-1-88179-0-az.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-88179-0_AZ_c-1-88179-0-az.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Extraction Tool for Flexible Flat Cable (FFC)

English

Agency Approvals

CSA Certificate

English