




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECR-23-163258	16NOV2023	P.C	D.Z

POSITION 1 IDENTIFICATION FEATURE




1 MATERIAL: HOUSING: THERMOPLASTIC NYLON66 UL94V-0. BLACK COLOR. CONTACTS: BRASS, TIN-PLATED

2. RECOMMENDED MATING PART: []-2029029-[]



24	46.2±0.25	51.6	55.6	2-2029134-4
22	42.0±0.25	47.4	51.4	2-2029134-2
20	37.8±0.25	43.2	47.2	2-2029134-0
18	33.6±0.25	39.0	43.0	1-2029134-8
16	29.4±0.25	34.8	38.8	1-2029134-6
14	25.2±0.25	30.6	34.6	1-2029134-4
12	21.0±0.25	26.4	30.4	1-2029134-2
10	16.8±0.13	22.2	26.2	1-2029134-0
8	12.6±0.13	18.0	22.0	2029134-8
6	8.4±0.13	13.8	17.8	2029134-6
4	4.2±0.13	9.6	13.6	2029134-4
2	-	5.4	9.4	2029134-2
POS	A	B±0.25	C±0.38	PART NUMBER



PCB LAYOUT: COMPONENT SIDE
RECOMMENDED BOARD THICKNESS 1.78

2-2029134-4 SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 13AUG2008		
DIMENSIONS: mm		CHK C. CASH 13AUG2008		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. CASH 13AUG2008	NAME	
0 PLC ±		PRODUCT SPEC	VERTICAL HEADER, BLACK, WITH PEGS, WITH DRAIN HOLES, VAL-U-LOK(TM)	
1 PLC ± 0.13		APPLICATION SPEC	SIZE	CAGE CODE
2 PLC ± 0.25		108-2112	A2	00779
3 PLC ± -		114-13172	DRAWING NO	C=2029134
4 PLC ± -		WEIGHT	SCALE	SHEET
ANGLES ±		-	10:1	1 of 1
FINISH		CUSTOMER DRAWING	REV	B
1				