

### Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.  |
| Solder Process Capability                     | Not applicable for solder process capability  |

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 2098378-4  
20P PLUG HOUSING KEY A



TE Part # 2098835-1  
20P HYBRID HEADER ASSEMBLY KEY




TE Part # 1-2098380-0  
20 POS HYBRID UNSEALED CAP KY-A  
STD CLIP

## Customers Also Bought



TE Part #926845P007  
FL2500-NO.3-J1-0-65MM



TE Part #623346-1  
2P CONNECTOR HOUSING



TE Part #CAT-M8793-CH8172  
MQS, CONNECTOR HOUSING



TE Part #2098377-2  
20P PLUG ASSEMBLY UNSEALED  
HYBRID B-KEY



TE Part #2208729-1  
COVER,OUTGOING VERTICAL,ASSY



TE Part #2209893-1  
BCM 14P MCP2.8 SOCKET



TE Part #2317734-1  
92POS,SOC HSG,CCS,UNSLD,COD 1



TE Part #2378779-1  
PLASTIC CARRIER,25POS,CODE A



TE Part #2177836-2  
COVER, 32POS. MQS, REVERSE,ASSY

## Documents

### Product Drawings

[20P PLUG ASSEMBLY UNSEALED HYBRID A-KEY](#)

English

### CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_2098377-4\\_A\\_c-2098377-4-a.2d\\_dxf.zip](#)



English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2098377-4\\_A\\_c-2098377-4-a.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2098377-4\\_A\\_c-2098377-4-a.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### **Instruction Sheets**

[Instruction Sheet \(U.S.\)](#)

English