



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2103124-1
HVA280 2P HEADER ASSY, KEY A


TE Part # 1587940-1
CABLE SEAL RETAINER, SIZE A

TE Part # 1587940-2
CABLE SEAL RETAINER, SIZE B

TE Part # 2-2141600-2
TAB 2.8x0.8 CONTACT CF SRC Ag



TE Part # 1587828-3
INNER FERRULE, SIZE C, HVA280-2PI



TE Part # YHVA280-2PHX-HDR-A
HVA280 2P (2103124-1) HEADER, KEY A



TE Part # 4-2103015-1
PLUG SUBASSY, A, HVA280-2PHM F



TE Part # 1587940-3
CABLE SEAL RETAINER, SIZE C



TE Part # 1587530-2
CABLE SEAL HVA SIZE C-D



TE Part # 1587829-3
OUTER FERRULE, SIZE C, HVA280-2PI



TE Part # 1587530-1
CABLE SEAL HVA SIZE A-B



TE Part # 1587829-2
OUTER FERRULE, SIZE B, HVA280-2PI



TE Part # 1587828-2
INNER FERRULE, SIZE B, HVA280-2PI

Customers Also Bought



TE Part #1-968853-3
AMP MCP 2.8, CONTACT



TE Part #2098641-1
2POS, MCON 1.2 CB REC 2p SL SEALED



TE Part #2-2141600-2
TAB 2.8x0.8 CONTACT CF SRC Ag



TE Part #2349180-2
DIA 4MM, TERMINAL, FAM SLD, CB



TE Part #2-2371113-1
2POS, DIA 4MM, PIN HSG ASSY, SLD, COD A




TE Part #1587828-3
INNER FERRULE, SIZE C, HVA280-2PI



TE Part #2103157-1
SHIELD, PLUG, SIZE 1, Sn, HVA280



TE Part #2103191-2
CAP SUBASSY, KEY B, HVA280-2PHI



Documents

Product Drawings
CAP SUBASSY, KEY A, HVA280-2PHI
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2103191-1_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_2103191-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_2103191-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Application Specification
English