2-1971875-4 ✔ ACTIVE

Power Triple Lock

TE Internal #: 2-1971875-4

12 Position, Cap, Housing, Crimp, Wire-to-Wire, UL 94V-0, 6 mm [.236 in] Centerline, 3 Row, 600 VAC, Wire & Cable, Power, Power Triple Lock

View on TE.com >

Connectors > Rectangular Connectors > Standard Rectangular Connectors > Standard Temperature Caps | POWER TRIPLE LOCK







Connector Product Type: **Housing**

Connector & Housing Type: **Cap**

Termination Method to Wire & Cable: **Crimp**

Connector System: **Wire-to-Wire**

Contact Retention Within Housing: **Without**

All Standard Temperature Caps | POWER TRIPLE LOCK (40)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Cap
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	12
Number of Rows	3
Number of Power Positions	12

Electrical Characteristics

Operating Voltage	600 VDC

Body Features

Connector & Keying Code	B
Primary Product Color	Purple
Cable Exit Angle	180°

Contact Features

Contact Layout	Matrix
Contact Retention Within Housing	Without
Contact Type	Tab

Termination Features

Termination Method to Wire & Cable	Crimp

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Latches
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	6 mm[.236 in]
Housing Material	PBT GF

Dimensions

Panel Thickness (Recommended)	1 – 2 mm[.039 – .079 in]
Connector Height	31.15 mm
Row-to-Row Spacing	8.1 mm[.319 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Circuit Application	Power

Identification Marking

Circuit Identification Feature	With

Industry Standards

Compatible With Agency/Standards Products	UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0

Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-P87074-T111
Tab Contact — POWER TRIPLE LOCK



TE Part # CAT-P87074-T669
Locking Plate, POWER TRIPLE LOCK, TPA



TE Part # 1452426-1
EXTRACTION TOOL



TE Part # 2-1971876-4
PTL 3X4 PLUG HSG STD TEMP KEY B PUR




TE Part # 1971789-1
CPA

Also in the Series | Power Triple Lock




Connector Contacts(26)



Connector Hardware(12)



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(21)



Power Contacts(26)



Rectangular Power Connectors(301)




Wire-to-Board Headers & Receptacles (21)

Customers Also Bought



TE Part #ASA158F12390235000
623 PLUG


TE Part #EC9833-000
ZHD-SCE-3.2-50-S1-4



TE Part #55992-1
TERMINAL,AMPOWER R 2/0 5/16



TE Part #1-1415543-5
RTE44110



TE Part #1614770-4
BDS 2 A 250 10R 10%



TE Part #ZPF000000000205378
CONTACT MALE ANG.90, CAL20, 120MM2 - FXP



TE Part #YZ-KC-212751A-PY00
TOOL DISMOUNTING - FXP2



TE Part #ZPF000000000205373
PLUG MALE ANG.90 CAL.20 - FXP



TE Part #ZPF000000000136485
RECEPTACLE MALE FOR 12 PINS, CAL1,6



TE Part #ZPF000000000205388
CONTACT FEMALE CAL.20, M12 - FXP

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1971875-4_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1971875-4_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1971875-4_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English