



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Pb (36.09% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #406732-2
MJ,10MM,8P,SHLD,NO HSG POST,SN




TE Part #3-647630-2
02P MTA100 HRD ASSY F/L LF



TE Part #1410188-3
MULTIGIG RT T2 7RW DC DF F-RGT




TE Part #1-1469492-2
MULTIGIG RT 9MM GUIDE/ESD 45 DEG




TE Part #2-1761608-8
IDC LOW PRO HDR 24P VERT SHT L




TE Part #2000676-7
Keyed Guide Pin, Machined




TE Part #2311768-1
AMPL REC, HD22, R/A, 26P, THREADED



TE Part #1410137-2
MULTIGIG RT T2 .8" DC DF F-CTR



TE Part #1410139-2
MULTIGIG RT T2 .8 DC DF F-RGT



TE Part #2226996-1
DC, 7ROW, P0, TRUE HALF, MULTIGIG RT 2-R

Documents

Product Drawings

MEZALOK, SKT, 114P, 12MM, 30AU, TL, UF

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English