293132-3 × OBSOLETE

TE Internal #: 293132-3

TE Internal Description: DUOPLUG 2.5 pitch, with External Walls

View on TE.com >

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Customers Also Bought



TE Part #1-172210-6

5 POS PL MK-2 187 HOUSING RECEPTACLE



TE Part #175149-2

AMP UNIVE. POWER CONN TAB CONT



TE Part #456408-1

CRIMPER, WIRE .110 F



TE Part #1-480702-0


04P UMNL PLUG HSG NATL



TE Part #1375819-1
CST-100 II CONTACT TIN PLT




TE Part #1745083-1
3 POS. PLUG ASSY AMP SUPERSEAL 1.5 SRS




TE Part #5-1803000-5
ANVIL, COMBINATION, END FEED



TE Part #5-2119785-4
CRIMPER, INSULATION OVERLAP PREMIUM



TE Part #284866-8
Direct mount card edge conn.,



TE Part #284931-7
DUOPLUG Standard, female conn.

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_293132-3_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_293132-3_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_293132-3_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

RAST Connector System Catalog

English

Product Specifications

Application Specification

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English