

327640 ✓ ACTIVE

SOLISTRAND | SOLISTRAND Budget

TE Internal #: 327640


SOLISTRAND Budget, Rings & Spades, Ring Tongue, 26 – 22AWG

Wire Size, .12 – .4mm² Wire Size, M2 / #2, Stud Diameter 2.36 mm [.093 in]

[View on TE.com >](#)



Terminals & Splices > Rings & Spades



Terminal & Splice Type: **Ring Tongue**

Wire Size: .12 – .4 mm²

Ring & Spade Stud Size: **#2, M2**

Stud Diameter: **2.36 mm [.093 in]**

Features

Product Type Features

Shape Description	RING-041
Ring & Spade Stud Size	#2, M2
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Inspection Slot	No
Ring & Spade Plating Material	Copper, Unplated

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight



Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	.12 – .4 mm ²
Stud Diameter	2.36 mm [.093 in]
Tongue Thickness	.79 mm [.031 in]
Ring & Spade Overall Length	8.74 mm [.344 in]
Barrel Inside Diameter	.91 mm [.036 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C [338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 323987
TERMINAL,BUDG R 24-20 8



TE Part # 55215-1
TERMINAL,SOLIS R 26-22 2



TE Part # 34261
TERMINAL,BUDG HK 22-16 6

Also in the Series | SOLISTRAND Budget



Knife Disconnects(4)



Rings & Spades(181)



Splices(1)

Customers Also Bought




TE Part #0462-201-20141
DEUTSCH SOLID CONTACTS



TE Part #1-480698-0
02P UMNL PLUG HSG NATL



TE Part #114017-ZZ
DEUTSCH SEALING PLUGS



TE Part #1-499786-2
AMP-LATCH UNIVERSAL HEADERS



TE Part #YDTS20F15-35PD0000
D38999: Square Flange, 15-35 insert



TE Part #1-1532174-7
M83513/04-D01C, MCKS-C2-B-25S6G1-18.0

Documents

Product Drawings

TERMINAL,BODY R 26-22 2

English