4-1333204-6 ✔ ACTIVE

TE Internal #: 4-1333204-6

TE Internal Description: ANVIL, COMB. (.080)

View on TE.com >



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Customers Also Bought




TE Part #456414-9
CRIMPER, WIRE 160F



TE Part #1333203-3
ANVIL, COMBINATION .070



TE Part #7-1333203-6
ANVIL, COMBINATION .070



TE Part #1333204-7
ANVIL, COMBINATION .080




TE Part #6-1633588-5
CRIMPER, WIRE 'F' ..096


TE Part #3-22278-9
SPRING,COMPRESSION



TE Part #4-238011-2
BLOCK, CRIMPER SPACER



TE Part #4-879500-2
AMBOSS



TE Part #1633689-3
ANVIL



TE Part #1633710-4
CRIMPER, INSULATION O .042

Documents

Instruction Sheets

Instruction Sheet (U.S.)

English