



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	26NOV2012	WI	WI
	B	ECN-22-137008	31JAN2022	LS	GS

CRIMPING HEAD SOLARLOK PV4 PIN AND SOCKET CONTACTS

CONTACT LOCATOR
TCPN 7-1579025-3
INCLUDED ON DELIVERY



1. PROCESSING OF TERMINALS ACCORDING TO APPLICATION SPECIFICATION 114-106078.
2. CRIMP HEAD USED IN COMBINATION WITH LONG HANDLES CSV10 VARIO, TCPN 2-1579005-2.
3. DIMENSION: 65x40x40MM (LxWxH)

CONTACT	WIRE SIZE mm ² / AWG	WIRE CRIMP		STRIPP LENGTH mm	INSTRUCTION SHEET
		HEIGHT mm	WIDTH mm		
1971857 (PIN) 1971858 (SOCKET) 2270251 (PIN) 2270226 (SOCKET) 2363118 (PIN) 2363117 (SOCKET)	4.0 / AWG12	2.14±0.05	3.94	6.5 ⁺¹ _{-0.05}	411-18554
1971857 (PIN) 1971858 (SOCKET) 2270251 (PIN) 2270226 (SOCKET) 2363118 (PIN) 2363117 (SOCKET)	6.0 / AWG12	2.49±0.05	3.94	6.5 ⁺¹ _{-0.05}	411-18554

© 2022 TE Connectivity. All Rights Reserved.

DIMENSIONS: mm	DWN C.WITT	26NOV2012	MATERIAL	-	FINISH	-
	CHK C.Witt	26NOV2012	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C.WITT	26NOV2012				
	0 PLC ±-	1 PLC ±-	2 PLC ±-	3 PLC ±-	4 PLC ±-	ANGLES ±1°
	PRODUCT SPEC	-	NAME SOLORLOK PV4 CRIMPING HEAD			RESTRICTED TO -
	APPLICATION SPEC	-	SIZE	CAGE CODE	DRAWING NO	
	WEIGHT	130g	A 4	00779	© = 4-1579016-7	
CUSTOMER DRAWING			SCALE	-	SHEET	1 OF 1
					REV	B