4-1803556-1 ✔ ACTIVE

TE Internal #: 4-1803556-1

TE Internal Description: CRIMPER, WIRE F

View on TE.com >



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	未针对中国 RoHS 符合性进行审核 Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts




TE Part # 2375592-2
OCEAN-2.0-APPLICATOR-S-130F-RSA



TE Part # 2375591-2
OCEAN-2.0-APPLICATOR-S-130F-RSA



TE Part # 7-2375592-7
OCEAN_2.0_SPARE_PART_KIT-130F



TE Part # 7-2375591-7
OCEAN_2.0_SPARE_PART_KIT-130F


Customers Also Bought




TE Part #2-456414-3
CRIMPER,WIRE .160 F



TE Part #4-657555-0
DRAHTCRIMPER



TE Part #9-1633131-1
ANVIL, COMBINATION .080



TE Part #8-1633138-3
ANVIL, COMBINATION



TE Part #1-1803095-4
FLOATING SHEAR, FRONT



TE Part #3-1803412-3
ANVIL, WIRE



TE Part #2358664-5
FLAP, ASSY, INLET COMBO 1, LEFT, LED



TE Part #2399668-2
H&S 95mm, Cable clip



TE Part #2402048-1
INLET HSG, CCS1 ASSY, WITH LED

TE Part #2234139-2
CRIMPER HVM HEX

Documents

Instruction Sheets

Instruction Sheet (U.S.)

English