
2MM-HSD-D20-VT-02-M-TB ✔ ACTIVE


TE Internal #: 4-2823342-0

TE Internal Description: 40P,2MM,SHRD HDR,DRVT,2.8,0.38AU,TB

View on TE.com >







Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 4-2316109-0
40P,2MM,REC,HSG,DR,CRIMP,LCK RAMP,BOX

Documents

Product Drawings

40P,2MM,SHRD HDR,DRVT,2.8,0.38AU,TB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-2823342-0_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-2823342-0_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-2823342-0_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Flyer - AMPMODU 2mm Shrouded Header

English

AMPMODU 2mm interconnection system QRG

English

Product Specifications

Application Specification

English