






P	LTR	DESCRIPTION	DATE	DWN	APV
	—	SEE SHEET 1	—	—	—




PCB PATTERN LAYOUT
GENERAL TOLERANCE ± 0.05





SECTION A-A
SCALE 1:1



BLACK	3.00	25.00	25.80	26.34	23.30	21.00	30	7-2394521-3	6-2394521-
	1.50	17.50	18.30	18.84	15.80	13.50	20	7-2394521-2	6-2394521-
		10.00	10.80	11.34	8.30	6.00	10	7-2394521-1	6-2394521-
NATURAL	3.00	25.00	25.80	26.34	23.30	21.00	30	5-2394521-3	4-2394521-
	1.50	17.50	18.30	18.84	15.80	13.50	20	5-2394521-2	4-2394521-
		10.00	10.80	11.34	8.30	6.00	10	5-2394521-1	4-2394521-
COLOR	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	Pos.No	TYPE 2	TYPE 1
								P/N	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Tommy Qian 12APR2021 CHK Niki Shi 12APR2021 APVD Niki Shi 12APR2021		 TE Connectivity Ltd.	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.5 1 PLC ± 0.25 2 PLC ± 0.15 3 PLC ± 0.1 4 PLC ± — ANGLES ± 2°		NAME 1.5mm PITCH WTB Conn. SMT R/A TYPE DOUBLE ROW —	
MATERIAL		FINISH		SIZE	RESTRICTED
NOTE 1		NOTE 2		CAGE CODE	DRAWING NO
		WEIGHT N/A		A3 00779	C-2394521
CUSTOMER DRAWING				SCALE	REV
				N/A	2 OF 7 A1

P	LTR	DESCRIPTION	DATE	DWN	APV
	—	SEE SHEET 1	—	—	—




PCB PATTERN LAYOUT
GENERAL TOLERANCE ± 0.05

- NOTES:
1. MATERIAL:
 - 1.1 HOUSING: THERMOPLASTIC, HIGH TEMP.,UL94V-0.
COLOR:SEE PART NUMBER
 - 1.2 CONTACT: Boway ALLOY .
 - 1.3 FITTING NAIL: STAINLESS STEEL
 2. FINISH:
 - 2.1 CONTACT:
50u" MIN NICKEL UNDERPLATING OVERALL.
TYPE 1: 100u" MIN MATT TIN PLATING OVERALL
TYPE 2: GOLD FLASH ON CONTACT AND SOLDER
 - 2.2 FITTING NAIL:
50u" MIN NICKEL UNDER PLATING OVERALL
100u" MATT MIN TIN PLATING OVERALL
 3. REFLOW SOLDER CAPABLE TO 260°C





SECTION A-A
SCALE 1:1



BLACK	3.00	32.50	33.30	33.84	30.80	28.50	40	3-2394521-4	2-2394521-
NATURAL	3.00	32.50	33.30	33.84	30.80	28.50	40	1-2394521-4	2394521-4
COLOR	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	Pos.No	TYPE 2	TYPE 1
								P/N	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Tommy Qian 12APR2021		 TE Connectivity Ltd.	
		CHK Niki Shi 12APR2021			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 1.5mm PITCH WTB Conn. SMT R/A TYPE DOUBLE ROW —	
		0 PLC ± 0.5 1 PLC ± 0.25 2 PLC ± 0.15 3 PLC ± 0.1 4 PLC ± — ANGLES ± 2°		APVD Niki Shi 12APR2021	
		PRODUCT SPEC —		APPLICATION SPEC —	
MATERIAL		FINISH		SIZE	RESTRICTED
NOTE 1		NOTE 2		CAGE CODE	DRAWING NO
				A3	00779
				©	2394521
CUSTOMER DRAWING				SCALE	REV
				N/A	3 of 7
					A1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




PCB PATTERN LAYOUT
GENERAL TOLERANCE ± 0.05


- NOTES:
1. MATERIAL:
 - 1.1 HOUSING: THERMOPLASTIC, HIGH TEMP.,UL94V-0.
COLOR:SEE PART NUMBER
 - 1.2 CONTACT: COPPER ALLOY BRASS.
 2. FINISH:
 - 2.1 CONTACT:
50u" MIN NICKEL UNDERPLATING OVERALL.
TYPE 1: 100u" MIN MATT TIN PLATING OVERALL
TYPE 2: GOLD FLASH ON CONTACT AND SOLDER
 3. REFLOW SOLDER CAPABLE TO 260°C



SECTION A-A
SCALE 1:1

BLACK	3.00	32.50	33.30	33.84	30.80	28.50	40	7-2394521-4	6-2394521-4
NATURAL	3.00	32.50	33.30	33.84	30.80	28.50	40	5-2394521-4	4-2394521-4
COLOR	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	Pos.No	TYPE 2	TYPE 1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Tommy Qian 12APR2021		 TE Connectivity Ltd.	
		CHK Niki Shi 12APR2021			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 1.5mm PITCH WTB Conn. SMT R/A TYPE DOUBLE ROW —	
		0 PLC ± 0.5 1 PLC ± 0.25 2 PLC ± 0.15 3 PLC ± 0.1 4 PLC ± — ANGLES ± 2°			
MATERIAL		FINISH		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
NOTE 1		NOTE 2		A3 00779 C-2394521 —	
CUSTOMER DRAWING				SCALE N/A SHEET 4 OF 7 REV A1	




- NOTES:
- 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE:±0.20mm
 - CARRIER CAMBER NOT TO EXCEED 1mm IN 250mm.
 - ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
 - MATERIAL: BLACK ANTI-STATIC POLYSTYRENE.
 - THICKNESS: 0.50 ± 0.05 mm.
 - PACKING LENGTH PER 13" REEL :7.5 METERS.
 - COMPONENT LOAD PER 13" REEL : 400 PCS.

24.4	11.65	9.06	6.96	24.00	11.50	10P	*-2394521-1
DIM D	DIM B2	DIM B1	DIM B0	DIM W	DIM F	POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± 0.5
1 PLC ± 0.25
2 PLC ± 0.15
3 PLC ± 0.1
4 PLC ± -
ANGLES ± 2°
FINISH -

MATERIAL

-

DWN Tommy Qian 12APR2021
CHK Niki Shi 12APR2021
APVD Niki Shi 12APR2021
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

CUSTOMER DRAWING




TE Connectivity Ltd.



1.25mm PITCH WTB Conn.
SMT VERTICAL TYPE DOUBLE ROW


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2394521	-

SCALE	SHEET	REV
N/A	5 of 7	A1




34.20	31.61	29.51	56.40	56.00	26.20	40P	*-2394521-4
26.71	24.12	22.02	44.40	44.00	20.20	30P	*-2394521-3
19.15	16.56	14.46	44.40	44.00	20.20	20P	*-2394521-2
DIM B2	DIM B1	DIM B0	DIM D	DIM W	DIM F	POS.	PART NUMBER




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Tommy Qian 12APR2021		 TE Connectivity Ltd.									
		CHK Niki Shi 12APR2021											
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 1.25mm PITCH WTB Conn. SMT VERTICAL TYPE DOUBLE ROW —									
		0 PLC ± 0.5 1 PLC ± 0.25 2 PLC ± 0.15 3 PLC ± 0.1 4 PLC ± — ANGLES ± 2°											
MATERIAL —		FINISH —											
		WEIGHT —		SIZE A3		CAGE CODE 00779	DRAWING NO C-2394521		RESTRICTED TO —				
CUSTOMER DRAWING								SCALE N/A		SHEET 6 OF 7		REV A1	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




- NOTE:
1. STAPLES SHOULD ONLY BE USED TO SET UP CARTON
ALL CARTONS CLOSURES MUST BE DONE WITH TAPE.
 2. FILL PACKAGING REEL WITH THE QUANTITIES AS INDICATED



2000(PCS)	400(PCS)	5	40P	*-2394521-4
2800(PCS)	400(PCS)	7	30P	*-2394521-3
2800(PCS)	400(PCS)	7	20P	*-2394521-2
4400(PCS)	400(PCS)	11	10P	*-2394521-1
PARTS PER CARTON	PARTS PER REEL	REELS PER CARTON	POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Tommy Qian 12APR2021	 TE Connectivity Ltd.		
		CHK Niki Shi 12APR2021			
		APVD Niki Shi 12APR2021	NAME		
		PRODUCT SPEC	1.5mm PITCH WTB Conn. SMT VERTICAL TYPE DOUBLE ROW		
		APPLICATION SPEC	—		
		WEIGHT N/A	SIZE A3	CAGE CODE 00779	DRAWING NO C-2394521
		CUSTOMER DRAWING	SCALE N/A	SHEET 7 OF 7	REV A1

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ± 0.5	
		1 PLC ± 0.25	
		2 PLC ± 0.15	
		3 PLC ± 0.1	
		4 PLC ± —	
		ANGLES ± 2°	
MATERIAL —		FINISH —	