



All Signal Relays: 5 Amp, Monostable DC (0)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought

TE Part #1SNA356100R1500
DBT17-BL

TE Part #NB42782001
RNF-100-3/16-4-STK

TE Part #2065124003
HFT5000-20/10-0-SP

TE Part #34150
PG R 22-16 COMM 22-18 MIL 1/4

TE Part #34162
TERMINAL,PG R 16-14 1/4

TE Part #36964
SPLICE,CE 22-14

TE Part #130171
TERMINAL, PIDG, RT, 12-10 AWG, M5

TE Part #1546413-3
ETHERNET RJ-45 BLKHD PASSTHRU

TE Part #8-1393808-3
V23154D 721B110

TE Part #1981944-1
Industrial Ethernet Strip tool

Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-1393806-7_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-1393806-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-1393806-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

- Product Specifications

Definitions General Purpose Relays

English



Product Specification

English