




Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #3-647050-6
06P MTA100 HDR ASSY F/L HITEMP



TE Part #1-1462051-7
HF3 54 = 50OHM 140MW 6V MONO



TE Part #2-1462051-5
HF3 92S = 50OHM 140MW 4.5V BIST 2COIL




TE Part #1617030-2
HFW1201B00 = HFW 1/2 SIZE RELA 2COIL




TE Part #1982295-5
ELCON MINI 2P RA HEADER,TRAY,W/ CODING




TE Part #5747461-6
HD-20 RCPT 25P RA 590 FFSCRLK




TE Part #1734709-7
1.0 WTB HDR SR RA 7 POS



TE Part #1734709-9
1.0 WTB HDR SR RA 9 POS



TE Part #6-1437418-0
J74=JUMPER SPADE TYPE 7/16



TE Part #1052565-1
2052 1618 00

Documents

Product Drawings

MTA100 CONT 28 AWG TPBR LP

English

CAD Files

Customer View Model

ENG_CVM_641646-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_641646-2_D.3d_stp.zip

English

Customer View Model

ENG_CVM_641646-2_D.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Product Specification

English