

7-2266111-8 ✓ ACTIVE

TE Internal #: 7-2266111-8

TE Internal Description: OCEAN_2.0_CONVERSIONKIT_DEUTSCH-074F052O

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-2266111-1
OCEAN_2.0_APPLICATOR-S-074F052O-RSM



TE Part # 5-2266111-2
OCEAN_2.0_APPLICATOR-S-074F052O-RSA



TE Part # 2266111-1
OCEAN_2.0_APPLICATOR-S-074F052O-RSM



CRIMPER REPRESENTATION ONLY
TE Part # 4-1633713-1
CRIMPER, WIRE PREMIUM

TE Part # 1-286504-4
SOCKET 1062-16-0677



ANVIL REPRESENTATION ONLY
TE Part # 1803293-7
ANVIL, COMBINATION DEUTCH STYLE

TE Part # 286504-4
SOCKET



TE Part # 2266111-2
OCEAN_2.0_APPLICATOR-S-074F052O-RSA



TE Part # CAT-D48-SFT273
DEUTSCH Stamped and Formed Contacts



CRIMPER REPRESENTATION ONLY
TE Part # 1803019-8
CRIMPER, INSULATION O

Customers Also Bought



TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #DT06-2S
PLG, 2P, GRY, N




TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING

Documents



Product Drawings

[OCEAN_2.0_CONVERSIONKIT_DEUTSCH-074F052O](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English