



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

Applicator & Product Style	OCEAN
----------------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



CRIMPER REPRESENTATION ONLY

TE Part # 6-1633962-8


[CRIMPER, INSULATION F PREMIUM](#)

Customers Also Bought




TE Part #CP4904-000

[ES2000-NO.1-C1-0-65MM-SH](#)



TE Part #172217-1

[FF 250 REC HSG 2P NYLON NAT](#)



TE Part #1333225-1

[ANVIL, COMBINATION SPECIAL](#)




TE Part #2-2119582-7

[Crimper, Insulation F Premium](#)



TE Part #2151144-1

[OCEAN_2.0_APPLICATOR-S-067F062F-RSM](#)




TE Part #184394-1

[2X2 PLG ASY W/RET W/O CPA C3-A](#)



TE Part #917067-6

[040-2 TAB CONT S GOLD 22-18](#)



TE Part #173858-4

[070 MULTILOCK CAP ASSY 12P GRN](#)



TE Part #316157-2

[SEAL RUBBER 2P SEALED D/MIRROR](#)

Documents

Product Drawings

[OC-050F055F-CRIMPTOOLINGKIT](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

