

734790-1 ✓ ACTIVE

TE Internal #: 734790-1

TE Internal Description: SERVICE TOOL

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #66101-3
III+ SKT, 18-16, 15AU/FL, LP




TE Part #182641-1
17-14 CPC SQ FLANGE RECPT RS




TE Part #967376-2
FLA-STE-GEH KPL16P



TE Part #6-1393211-2
T92P7A22-240



TE Part #1-1633920-9
ANVIL, COMBINATION




TE Part #1-2112891-6
36POS, TAB 1.5X0.6, TAB HSG, ASSY



TE Part #8-904741-3
CRIMPER, INSUL "O" (.170")



TE Part #1320928-1
STRIP GUIDE



TE Part #8-1579002-0
SUPER CHAMP III



TE Part #2359941-2
96POS, MCON-1.2 CB, REC HSG, ASSY

Documents

Instruction Sheets

Instruction Sheet (non U.S.)

German

Instruction Sheet for Hand Tool 734790-1 with Die Set 734761-1

German