
796608-4 ✔ ACTIVE

TE Internal #: 796608-4

TE Internal Description: 6WWV-09-006=#6 TRIBARRIER

View on TE.com >







Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 2-796608-1
6WWV-09-008=#6 TRIBARRIER

Customers Also Bought




TE Part #1-292228-6
1.5 MINI CT SGL H SMT W/O BOSS




TE Part #292231-3
1.5 MINI CT SGL V SMT W/O BOSS



TE Part #2-1658012-3
MSB0.80RC-ASY120FL,-,10,-TY



TE Part #1658017-3
MSB0.80PL19ASY120FL,-,10,-TY



TE Part #3-1879280-1
RP 2A 178K 0.1% 15PPM CUT LENG



TE Part #9-1879352-1
RR02 5% 1K8 AMMO



TE Part #4-1879499-9
CRGH2010 5% 100R 1W



TE Part #2176347-6
CRGCQ 2010 27R 1%



TE Part #2267077-1
TMS1T4B5M2RE



TE Part #1-6609027-5
10EK7=F7095 S0

Documents

Product Drawings

6WWV-09-006=#6 TRIBARRIER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_796608-4_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_796608-4_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_796608-4_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS

English

BUCHANAN_TERMINAL_BLOCKS_CATALOG

English

1-1773458-2_BARRIER_STRIPS_QUICK_REFERENCE_GUIDE

English

Agency Approvals

UL

English