



Our commitment. Your advantage.

Search

[Products](#) [Documentation](#) [Resources](#) [My Account](#) [Customer Support](#)

[Home](#) > [Products](#) > [By Type](#) > [Terminal Blocks & Strips](#) > [Product Feature Selector](#) > Product Details

SSB6FP250202 Product Details

[Live Product Chat](#)



Barrier Strips, Barrier Strip Sockets

[Not reviewed for RoHS Compliance](#)

Product Highlights:

- Barrier Strip
- Barrier Style = Single Row, Dual Barrier
- Block Style = Flat
- 9.53 mm Centerline
- Vertical Mount Angle

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

SSB6FP250202

(8-1437413-9)

TE Internal Number: 8-1437413-9

Obsolete

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

[Contact Product Information Center](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Barrier Strip
- [Mount Angle](#) = Vertical
- Number of Positions = 25
- CSA File No. = LR49571
- UL Recognized = File No. E60980
- Screw Material = Steel
- Mounting Ears = Without
- Comment = Do not order Screw and Captive Clamp in combination with other top hardware.; Other options available upon request, consult our Product Information Center.

Mechanical Attachment:

- Screw Plating = Bright Zinc/Chrome
- Mounting Style = Direct (All Positions Filled)

Electrical Characteristics:

- [Top Hardware](#) = Wire Clamp Combo Head
- Number of Levels = Single
- End Barriers = With
- Bracket = Without
- Mounting Insert = Without

Body Related Features:

- [Barrier Style](#) = Single Row, Dual Barrier
- [Block Style](#) = Flat
- [Centerline \(in \[mm\]\)](#) = 0.375 [9.53]
- Number of Rows = Single
- [Terminal Style](#) = Printed Circuit Pin 5.08 [.200]

Contact Related Features:

- Mounting Options = None

Industry Standards:

- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

Other:

- Brand = Buchanan

[Provide Website Feedback](#) | [Need Help?](#)