



EMI & EMC Solutions > EMC Chokes > EMC / RFI Chokes RR1000 - Stackable Chokes for Reliable EMI Mitigation



Product Orientation: Vertical

Product Mount Type: Chassis Mount

[All EMC / RFI Chokes RR1000 - Stackable Chokes for Reliable EMI Mitigation \(6\)](#)

Features

Body Features

Product Weight	1180 g[41.62 oz]
Product Orientation	Vertical

Mechanical Attachment

Product Mount Type	Chassis Mount
--------------------	---------------

Dimensions

Product Width	36 mm[1.41 in]
Product Length	200 mm[7.87 in]
Product Height	152 mm[5.98 in]

Usage Conditions

Operating Temperature Range	-40 – 100 °C[-40 – 212 °F]
-----------------------------	----------------------------

Operation/Application

Cooling Method	Natural Convection
----------------	--------------------

Industry Standards

Certified To	IEC 60938-3
--------------	-------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Also in the Series | Schaffner RR-Series



EMC Chokes(6)

Customers Also Bought



TE Part #HDC34-18
DUST CAP, 18SZ, PLG, AL, LANYARD, HD30



TE Part #DRCP28-86SA
PLG, 86P, BLK, 12/20, A



TE Part #CAT-PA3-RR
EMC / RFI Chokes RR1000 - Stackable Chokes for Reliable EMI Mitigation



TE Part #DRCP28-86SC
PLG, 86P, BLK, 12/20, C



TE Part #1-794606-2
MICRO MNL RPT CNT STRP 30AU LF



TE Part #1-794609-1
PIN CONT 26-30 15 GOLD STRIP



TE Part #794615-6
PANEL MT DBL ROW HSG 6 POS



TE Part #CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM, HOUSING

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_822866-SF_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_822866-SF_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_822866-SF_A.3d_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RFI Chokes RR1000

English

