





TABLE 1

PIN ARRANGEMENT
A-CODE

T411100X02X-000	T411100X03X-000	T411100X04X-000
T411100X05X-00X	T411100208X-00X	

T4111002081-001	RPC-M12-MS-8CON-PG9-MU-LN
T4111002051-001	RPC-M12-MS-5CON-PG9-MU-LN
T4111002081-000	RPC-M12-MS-8CON-PG9-MU
T4111001081-000	RPC-M12-MS-8CON-PG7-MU
T4111001082-000	RPC-M12-MS-8CON-PG7-M
T4111002051-000	RPC-M12-MS-5CON-PG9-MU
T4111001051-000	RPC-M12-MS-5CON-PG7-MU
T4111002052-000	RPC-M12-MS-5CON-PG9-M
T4111001052-000	RPC-M12-MS-5CON-PG7-M
T4111002041-000	RPC-M12-MS-4CON-PG9-MU
T4111001041-000	RPC-M12-MS-4CON-PG7-MU
T4111002042-000	RPC-M12-MS-4CON-PG9-M
T4111001042-000	RPC-M12-MS-4CON-PG7-M
T4111002031-000	RPC-M12-MS-3CON-PG9-MU
T4111001031-000	RPC-M12-MS-3CON-PG7-MU
T4111002032-000	RPC-M12-MS-3CON-PG9-M
T4111001032-000	RPC-M12-MS-3CON-PG7-M
T4111002021-000	RPC-M12-MS-2CON-PG9-MU
T4111001021-000	RPC-M12-MS-2CON-PG7-MU
T4111002022-000	RPC-M12-MS-2CON-PG9-M
T4111001022-000	RPC-M12-MS-2CON-PG7-M
TE PN	TYPE

T411100XXXX-000

CONTACT FINISH:
1: GOLD OVER NICKEL
2: SILVER OVER NICKEL

NUMBERS OF PINS:
02: 2 PINS
03: 3 PINS
04: 4 PINS
05: 5 PINS
08: 8 PINS

CABLE OUTLET:
1: PG7(CABLE FEED: 4-6mm)
2: PG9(CABLE FEED: 6-8mm)

BRAND:
T: W/ TE LOGO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±0.2
1 PLC	±0.2
2 PLC	±0.2
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	-

DWN
HAO WANG
08OCT2015

CHK
KOBBY ZHAO
08OCT2015

APVD
XIANG XU
08OCT2015

PRODUCT SPEC
108-106140

APPLICATION SPEC
114-137144

WEIGHT
-

Customer Drawing

NAME
M12 MALE, A CODE, STRAIGHT
UNSHIELDED CONNECTOR
SCREW TERMINAL

SIZE
A2

CAGE CODE
-

DRAWING NO
C-T411100XXXX000

RESTRICTED TO
-

SCALE
1:1

SHEET
1

OF
1

REV
B1

TE Connectivity