

696730-1 Product Details

[Share](#) | [Print](#) | [Email](#)


✓ Active

Splices - Closed Barrel

PIDG 16-14HD BUTT SPLICE

696730-1

TE Internal Number: 696730-1

Product Highlights [View All](#)

- Splice
- Not Sealed
- Splice Type = Butt
- Butt Splice Type = Standard
- Body Style = PIDG

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type [?]	Splice
Sealed [?]	No
Splice Type [?]	Butt
Insulation [?]	Yes
Insulation Support [?]	Insulation Support
Finish [?]	Tin
Color	Yellow

Termination Features	
Wire/Cable Size (CMA) [?]	2,050 - 5,180

Dimensions	
Insulation Diameter (mm [in]) [?]	3.81-5.84 [.150-.230]

Body Features	
Butt Splice Type [?]	Standard
Body Style [?]	PIDG
Wire Range (mm [AWG]) [?]	1.25-2.00 ² [16-14]
Material [?]	Copper

Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance [?]	RoHS compliant, ELV compliant
Lead Free Solder Processes [?]	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Packaging Features	
Packaging Method [?]	Loose Piece

Other	
Brand	TE Connectivity
Node Classification	Splices

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

- Corporate Information**
- [About TE](#)
 - [Investors](#)
 - [News Room](#)
 - [Supplier Portal](#)
 - [Careers](#)
 - [Terms & Conditions](#)
 - [Privacy Policy](#)
 - [Global Accessibility Statement](#)

- Quick Links**
- [Distributor Inventory](#)
 - [Product Cross Reference](#)
 - [Documents & Drawings](#)
 - [Product Compliance Support Center](#)
 - [Site Map](#)

- Customer Support**
- [Email or Chat With Us](#)
 - [Find a Phone Number](#)
 - [Knowledge Base](#)
 - [Manage Your Account](#)

Keep Me Informed

