

OBSOLETE	0,204 THK.	PRE-TIN	PHOS. BRONZE	343445-2
	0,204 THK.	POST-TIN	BRASS	343445-1
	OTHER TREATMENT	FINISH	MATERIAL	PART NUMBER
REFERENCE ONLY BE UP-DATED	CUSTOMER DWG		RELEASED FOR PUBLICATION AUGUST 1965	
	FOR REFERENCE ONLY		© COPYRIGHT 1965 BY AMP OF GREAT BRITAIN LTD. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY BRITISH AND FOREIGN PATENTS AND/OR PATENTS PENDING.	
			TOLERANCES UNLESS OTHERWISE STATED:-	INS. DIA. RANGE 2.20-2.70
			DEC $\pm$ 0.5	WIRE RANGE 0.75-2.0 mm²
			ANGLES $\pm$ 1°	SCALE 20:1
A	EB00-0089-03	SS	4-02-03	AMP of Great Britain Ltd. TERMINAL HOUSE STANMORE MIDDX.
2	REVISED	J.P	6.11.66	NAME
1	FIRST ISSUE	C.B	13.8.65	AMP-IN-MINI (SPECIAL)
ISS	REVISION RECORD	DR	DATE	A2 LOC. DWG. NO. SHEET E C 343445 1 of 1