




1000±25.4	[39.37±1.00]	1-636326-1
13000±76.2	[520.20± 3.00]	636326-6
5000± 50.8	[196.85±2.00]	636326-4
3000± 50.8	[118.11±2.00]	636326-3
2000±25.4	[78.74±1.00]	636326-2
1000±25.4	[39.37±1.00]	636326-1
L		PART NO


1 LABEL LOCATED APPROXIMATELY WHERE SHOWN.
LABEL TO READ AS FOLLOWS:

TYCO ELECTRONICS 636326-X YYWW ***	COMPANY NAME TYCO ELECTRONICS P/N DATE CODE COUNTRY OF ORIGIN
---	--

2 REMOVED


3. SEE SHEET 2 FOR WIRING SCHEMATIC

2	2	2	2	2	2	EA	-	PLUG ASSEMBLY, CABLE CONNECTOR, 0.8mm CHAMP	9
-	-	-	-	-	-	-	-	NOT REQUIRED	8
1	1	1	1	1	1	EA	-	LABEL	7
4.0	43.35	17.2	0.6	7.3	4.0	FT	-	CABLE (25) PAIR	6
4	4	4	4	4	4	EA	-	LATCH,SPRING	5
4	4	4	4	4	4	EA	-	BACKSHELL,PLATED	4
4	4	4	4	4	4	EA	-	BACKSHELL COVER	3
4	4	4	4	4	4	EA	-	TERMINAL COVER	2
-	-	-	-	-	-	EA	-	.8MM CHAMP PLUG ASSY	1
1--1	-6	-4	-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BECKER 20MAR06	 Tyco Electronics Corporation Harriaburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK P. BECKER 20MAR06	NAME CABLE ASSY			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D P. BECKER 20MAR06	PRODUCT SPEC APPLICATION SPEC WEIGHT A1 00779 C=636326 CUSTOMER DRAWING			
0 PLC ± -						
1 PLC ± -						
2 PLC ± -						
3 PLC ± -						
4 PLC ± -						
ANGLES ± -						
FINISH						
MATERIAL -			SIZE A1	CAGE CODE 00779	DRAWING NO C=636326	RESTRICTED TO
			SCALE NTS	SHEET 1	OF 2	REV F

LOC	DIST	REVISIONS				
		REV	DATE	BY	APP'D	
CF	71	—	—	—	—	—

WIRING SCHEMATIC
& COLOR CODE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BECKER 20MAR06	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK P. BECKER 20MAR06	NAME	
		APPROV P. BECKER 20MAR06	CABLE ASSY	
		PRODUCT SPEC	—	
		APPLICATION SPEC	—	
MATERIAL —	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± .1 1. PLC ± .1 2. PLC ± .1 3. PLC ± .1 4. PLC ± .1 ANGLES ± .1	SIZE A1	CAGE CODE 00779	DRAWING NO 636326
CUSTOMER DRAWING		WEIGHT —	RESTRICTED TO —	
SCALE NTS		SHEET 2 OF 2		REV F