





		REVISIONS						
P	F	ZONE	LTR	DESCRIPTION			DATE	APP
			J	REVISED PER EC 051A-0055-99			27AUG99	JG






TERMINATED VIEW WITH STRAIN RELIEF ASSEMBLED



- 1 UL RATED 94V-0 THERMOPLASTIC, COLOR: BLACK.
- 2 PHOSPHOR BRONZE PER QQ-B-750.
- 3 PLATED WITH .000030 GOLD ON LOCALIZED GOLD PLATE AREA, .000100 - .000200 BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.
- 4 POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSN #1 INDICATOR ON 10 AND 14 POSN PRODUCT.



DETAIL Z
SCALE 10:1
TYPICAL



1-746288-3	1-499252-1	1.125	2.100	2.380	2.150	43	44	1-746094-3
OBSOLETE		1.625	3.100	3.380	3.150	63	64	1-
OBSOLETE		1.525	2.900	3.180	2.950	59	60	1-
1-746288-0	499252-4	1.275	2.400	2.680	2.450	49	50	1-
746288-9	499252-1	1.025	1.900	2.180	1.950	39	40	
746288-8	499252-6	.875	1.600	1.880	1.650	33	34	
OBSOLETE		.775	1.400	1.680	1.450	29	30	
746288-6	499252-3	.675	1.200	1.480	1.250	25	26	
OBSOLETE		.625	1.100	1.380	1.150	23	24	
746288-4	499252-2	.525	.900	1.180	.950	19	20	
746288-3	499252-8	.425	.700	.980	.750	15	16	
746288-2	499252-9	.375	.600	.880	.650	13	14	
746288-1	499252-5	.275	.400	.680	.450	9	10	746094-1
RCPT KIT STRAIN RELIEF SUPERSEDED BY		E	D	C	B	A	NO OF POSN	PART NUMBER

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON : DECIMALS ± .005 ANGLES ± 5°	CONTRACT NO		AMP AMP INCORPORATED Harrisburg, Pa.		
	DR	J. PEACHEY 9-30-85			
	CHK	W.E. ZELKO 11-22-85			
	APPD	JAY SAUDER 11-22-85			
MATERIAL	APPD	D. HOFFMAN 11-25-85	RECEPTACLE KIT, AMP-LATCH NOVO, CTR & MIL PLZN, 30 GOLD DUPLEX CONTACTS, W/STRAIN RLF		
MOLDED PARTS: 			SIZE 	FSCM NO 00779	DRAWING NO 746094
CONTACTS: 					
FINISH	DSGN APPD		SCALE 4: 1		SHEET 1 of 1
CONTACTS: 	OTHER APPD				