


## Product Details for FSK -24.5A -4



### FSK -24.5A -4

Tyco Part Number: 3 - 1437214 - 5

[Active](#)

## FLEXSTRIP® Jumpers

[RoHS Compliant \(Statement of Compliance\)](#)

### Product Highlights:

- ? 2.54 mm Centerline
- ? Kapton Insulation Material
- ? Insulation Length = 114.30 mm
- ? Pin Arrangement (Left) = A
- ? Pin Arrangement (Right) = A

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

## Documentation & Additional Information

### Product Drawings:

- ? [None Available](#)

### Catalog Pages/Data Sheets:

- ? [None Available](#)

### Product Specifications:

- ? [None Available](#)

### Application Specifications:

- ? [None Available](#)

### Instruction Sheets:

- ? [None Available](#)

### CAD Files:

- ? [None Available](#)

### Additional Information:

- ? [Product Line Information](#)

### Additional Product Images:

- ? [Product View](#)
- ? [Product View](#)

### Related Products:

- ? [Tooling](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- ? [Insulation Material](#) = Kapton
- ? [Number of Conductors](#) = 4

### Mechanical Attachment:

- ? Impedance (?) = 117

### Electrical Characteristics:

- ? Current Rating (Amps.) = 3
- ? Voltage Rating (VAC) = 300

### Body Related Features:

- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- ? [Insulation Length \(mm \[in\]\)](#) = 114.30 [4.500]

### Configuration Related Features:

- ? [Pin Arrangement \(Left\)](#) = A
- ? [Pin Arrangement \(Right\)](#) = A

### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

### Conditions for Usage:

- ? Operating Temperature (°C [°F]) = -40 – +150 [-40 – +302]

### Other:

- ? Brand = Tyco Electronics