

Product Details for FSP - 23Z - 5

No Image Available

FSP - 23Z - 5

Tyco Part Number: 6 - 1437167 - 0

 [Active](#)

FLEXSTRIP® Jumpers

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? 2.54 mm Centerline
- ? Polyester Insulation Material
- ? Insulation Length = 76.20 mm
- ? Pin Arrangement (Left) = Z
- ? Pin Arrangement (Right) = Z

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [FLEXSTRIP PIN CONFIGURATIONS, GENERIC](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [Product View](#)
- ? [Product View](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Insulation Material](#) = Polyester
- ? [Number of Conductors](#) = 5

Mechanical Attachment:

- ? Impedance (?) = 113

Electrical Characteristics:

- ? Current Rating (Amps.) = 3
- ? Voltage Rating (VAC) = 300

Body Related Features:

- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- ? [Insulation Length \(mm \[in\]\)](#) = 76.20 [3.000]

Configuration Related Features:

- ? [Pin Arrangement \(Left\)](#) = Z
- ? [Pin Arrangement \(Right\)](#) = Z

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Operating Temperature (°C [°F]) = -40 – +105 [-40 – +221]

Other:

- ? Brand = Tyco Electronics