


## S05MTA235 Product Details



S05MTA235

TE Internal Number: 3-1618259-6

 **Obsolete**

[Contact Product Information Center](#)

### High Voltage Relays

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O
- Power Switching = No
- Contact Current Rating = 0 - 5 A
- Not RF Rated
- Coil Voltage = 12 VDC

[View all Features](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Termination Style](#) = PCB Tail

#### Electrical Characteristics:

- [Contact Current Rating \(A\)](#) = 0 - 5
- [RF Rated](#) = No
- [Coil Voltage \(VDC\)](#) = 12
- [Voltage, Max. \(VDC\)](#) = 0 - 15000
- [Current, Carry Only](#) = Yes

#### Termination Related Features:

- [High Voltage Connection \(Power\)](#) = PCB Tail
- [High Voltage Connection \(Coil\)](#) = PCB Tail
- [Auxiliary Contacts](#) = Without

#### Body Related Features:

- [Mount Style](#) = Printed Circuit Board

#### Configuration Related Features:

- [Contact Arrangement](#) = 1 Form A, SPST-NO, 1 N/O
- [Power Switching](#) = No
- [Economizer](#) = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

#### Other:

- [Brand](#) = Kilovac

 [BOOKMARK](#) 

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:



### Visit Us On:

