



926101-1 Product Details

[Share](#) [Print](#) [Email](#)


Active
 [View 3D PDF](#)

.240, .295" Centerline, 250 v, 28 A max. (.140" MATE-N-LOK)

02P PIN HOUSING

926101-1

TE Internal Number: 926101-1

Product Highlights [View All](#)

- Connector
- Housing
- 6.10 mm Centerline, Matrix
- Connector Style = Receptacle
- Contact Type = Pin

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Connector
Connector Type	Housing
Color	Natural
Connector Line	.140 MATE-N-LOK
Lock Type	Positive Lock
Mechanical Attachment	
Mount	Free Hanging
Electrical Characteristics	
Voltage (VAC)	250
Contact Features	
Contact Type	Pin
Contact Layout	In-Line
Housing Features	
Centerline, Matrix (mm [in])	6.10 [.240]
Connector Style	Receptacle
Housing Material	Polyamide 6.6 GF

Configuration Features	
Number of Positions	2
Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
Conditions for Usage	
Applies To	Wire/Cable
Packaging Features	
Packaging Method	Bag/Box
Packaging Quantity	1,000
Other	
Brand	AMP

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Feedback

Corporate Information
[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms of Use of TE.com](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links
[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)
[Terms & Conditions of Sale](#)

Customer Support
[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed