




What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Input/Output (Box to Box) > Product Feature Selector > Product Details

1-2007637-8 Product Details

Share Print Email



1-2007637-8

TE Internal Number: 1-2007637-8
 Active

Pluggable Connectors, Cages & Accessories

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- SFP+ Product Line
- Cage Assembly with Integrated Connector
- SFP+ Enhanced EMI Application
- Connector Style = Receptacle
- Cage Type = Stacked

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

Feedback

Documentation & Additional Information

Product Drawings:

- [CAGE AND PT CONNECTOR ASSEMBLY, WITH EMI SPRINGS, PR... \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [SFP+ Stacked Connector and Cage Assemblies \(PDF, English\)](#)

Application Specifications:

- [Stacked Small Form-Factor Pluggable \(SFP+\) Connector... \(PDF, English\)](#)

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Line = SFP+
- Product Type = Cage Assembly with Integrated Connector

Mechanical Attachment:

- PCB Mount = Single Sided

Electrical Characteristics:

- Data Signal Rate (Gb/s) = Up to 16

Termination Features:

- Termination Method to PC Board = Through Hole - Press Fit

Dimensions:

- Tail Length (mm [in]) = 3 [0.118]
- PCB Thickness, Recommended (mm [in]) = 1.50 [0.059]
- Length (X-Axis) (mm [in]) = 63.25 [2.490]
- Width (Z-Axis) (mm [in]) = 28.91 [1.138]
- Profile Height (Y-Axis) (mm [in]) = 25.50 [1.0039]

Contact Features:

- [Contact Plating, Mating Area, Material](#) = Gold or Gold Flash over Palladium Nickel
- Contact Base Material = Copper Alloy

Housing Features:

- Connector Style = Receptacle
- [Cage Type](#) = Stacked
- Housing Material = Liquid Crystal Polymer (LCP)
- Housing Color = Black
- Cage Material = Nickel Silver

Configuration Features:

- Port Configuration = 2x2
- Lightpipe = Without
- EMI Containment = External Springs

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant
- [UL Flammability Rating](#) = UL 94V-0

Conditions for Usage:

- Applies To = Printed Circuit Board

Operation/Application:

- [Application](#) = SFP+ Enhanced EMI

Packaging Features:

- Packaging Method = Box/Carton

Other:

- Brand = TE Connectivity

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

