

# 2-1106449-5 Product Details

[Share](#) [Print](#) [Email](#)


## HTS Connectors and Accessories

HB.16.STS.1.M25.G  
**2-1106449-5**   
 TE Internal Number: 2-1106449-5

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

[Feedback](#)

**Active**  
[View 3D PDF](#)

- Product Highlights** [View All](#)
- HB Series
  - Accessory
  - Accessory Type = Hood
  - Product Size = 6
  - Locking Device Type = Side Clip at Housing Bottom

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**  
 Use the Product Drawing for all design activity

Product Type Features	
Product Type	Accessory
Accessory Type	Hood
Product Size	6
Thread Size	M25

  

Body Features	
Entry Style	Side
Dimensions (L x H x W) (mm [in])	93.5 x 60.0 x 43.0 [3.68 x 2.36 x 1.69]
Material	Die Cast Aluminum

  

Contact Features	
Corrosion Protected	No

Configuration Features	
Locking Device Type	Side Clip at Housing Bottom

  

Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

  

Packaging Features	
Packaging Method	Loose Piece

  

Other	
Series	HB
Brand	HTS

**Related Products**

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

- Corporate Information**
- [About TE](#)
  - [Investors](#)
  - [News Room](#)
  - [Supplier Portal](#)
  - [Careers](#)
  - [Terms & Conditions](#)
  - [Privacy Policy](#)
  - [Global Accessibility Statement](#)

- Quick Links**
- [Distributor Inventory](#)
  - [Product Cross Reference](#)
  - [Documents & Drawings](#)
  - [Product Compliance Support Center](#)
  - [Site Map](#)

- Customer Support**
- [Email or Chat With Us](#)
  - [Find a Phone Number](#)
  - [Knowledge Base](#)
  - [Manage Your Account](#)

**Keep Me Informed**