

# 696638-1 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

## Ring and Spade Tongue Terminals

KIT-6,5/16,NI+RT555-.375X1.00

**696638-1**

TE Internal Number: 696638-1

**Product Highlights** [View All](#)

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Body Style = SOLISTRAND
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**  
Use the Product Drawing for all design activity

Product Type Features	
Receptacle Style	Straight
Barrel Type	Closed Barrel
Wire/Cable Type	Regular Wire
Insulation	No
Insulation Support	Non-Insulation Support
Stud Size	5/16 [M8]
Shape	RING-049
Heavy Duty	No
Finish	Tin
Termination Features	
Wire/Cable Size (CMA)	20,800 - 33,100
Dimensions	
Stud Diameter (mm [in])	8.33 [0.328]
Body Features	
Body Style	SOLISTRAND
Wire Range (mm [AWG])	13.00-15.00 <sup>2</sup> [6]
Material	Copper

Contact Features	
Terminal Shape	Ring Tongue
Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
Packaging Features	
Packaging Method	Loose Piece
Other	
Brand	TE Connectivity

**Related Products**

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)