




Search bar: What can we help you find?

Home > Products > Product Feature Selector > Product Details

1-520423-1 Product Details

Share | Print | Email



1-520423-1

SDL (Shielded Data Link)

Not EU RoHS or ELV Compliant (Find RoHS Compliant Alternates)

Product Highlights:

- Connector
- Cable Type = Flat
- Plug
- Product Series = 50 Series
- Receptacle Configuration = Standard

[View all Features](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

TE Internal Number: 1-520423-1

Superseded

[Search for Replacement Parts](#)

[View 3D PDF](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [SDL Systemj Connector \(PDF, English\)](#)

Application Specifications:

- [36-Series and 50-Series Flat-Cable SDL Plug Connectors \(PDF, English\)](#)

Instruction Sheets:

- [SDL Plugs and Receptacles \(PDF, English\)](#)
- [Crimping Die Assemblies 58261-1, 58261-2, 58261-3, a... \(PDF, English\)](#)

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version AF2\)](#)
- [3D Model \(IGES, Version AF2\)](#)
- [3D Model \(STEP, Version AF2\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Cable Type = Flat
- Gender = Plug
- Product Series = 50 Series
- Receptacle Configuration = Standard
- Wire Size (mm² [AWG]) = 0.12-0.15² [26], 0.2² [24]
- PCB Mount Retention = Without
- Shield Material = Copper Alloy

Dimensions:

- Conductor Insulation Diameter (mm [in]) = 1.14 - 1.27 [0.045 - 0.050]

Body Features:

- Shield Plating = Bright Tin-Lead

Contact Features:

- Contact Base Material = Copper Alloy
- Contact Plating, Mating Area, Material = Gold (50)

Housing Features:

- Housing Material = Polycarbonate GF
- Housing Color = Smoke Gray
- UL Flammability Rating = UL 94V-2

Configuration Features:

- Number of Conductors = 4

Industry Standards:

- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process
- Agency/Standard = CSA, UL

Identification Marking:

- Keying = A

Other:

- Brand = AMP
- Comment = Prefix no. designates key configuration. Suffix no. is a code for the number of conductors. Prefix & suffix nos. of plug assemblies must match those of the intended mating receptacle. Keys are molded in as an integral part of the plug & receptacle.

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

