

1060031 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



1060031 -1

[Active](#)

OS-2.9 (2.92mm) RF Connectors

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Connector
- ? Jack
- ? Terminate To Pin
- ? With Panel Attachment
- ? Panel Attachment Method = Flange

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [OS-2.9 2 HOLE FLANGE MOUNT JACK RECEPTACLE FIELD REP...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? [OS-2.9 Flange Mount Jack Receptacle Field Replaceabl...](#) (PDF, English)

CAD Files:

- ? None Available

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Connector
- ? Gender = Jack
- ? Comment = Field replaceable.; Accepts 0.3mm [.012] dia. pin; Captured Center Contact

Mechanical Attachment:

- ? Panel Attachment = With
- ? Panel Attachment Method = Flange

Body Related Features:

- ? Length (mm [in]) = 9.60 [0.378]
- ? Bushing Material = Beryllium Copper
- ? Bushing Finish = Gold over Nickel
- ? Support Bead Material = Noryl

Contact Related Features:

- ? Center Contact Material = Brass
- ? Center Contact Plating = Gold

Housing Related Features:

- ? Housing Material = Stainless Steel
- ? Housing Finish = Passivated

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Terminate To = Pin

Other:

- ? Brand = AMP