

## 1116377 -1 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



### Non - Metallic Cable Splices and Tap

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Cable Splice
- ? Number of Wires = 2 + ground

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**1116377 -1**

TE Part Number: 1116377 -1

[Active](#)

[Add to Part List](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [KIT,NMC CONNECTOR,2 COND+GND, 12 AND 14 AWG SOLID COPPER](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? [Nonmetallic Sheathed Cable Interconnection Devices](#) (PDF, English)

#### Instruction Sheets:

- ? [Nonmetallic \(Type NM -1\) Sheathed Cable Splicing ... \(1\)](#) (PDF, English)
- ? [Nonmetallic \(Type NM -1\) Sheathed Cable Splicing ... \(2\)](#) (PDF, English)

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Cable Splice
- ? Comment = 500 Housing/Contact assemblies in a polybag. 500 Strain Reliefs in a polybag. One bag of each packaged in a box with 5 instruction sheets.

#### Mechanical Attachment:

- ? Strain Relief Material = Polycarbonate

#### Electrical Characteristics:

- ? Current Rating (Amps.) = 20

#### Body Related Features:

- ? Number of Wires = 2 + ground
- ? Wire Range (mm [AWG]) = 2.00 -3.00 <sup>2</sup> [ 14 - 12]
- ? Wire Type = Solid
- ? Strain Relief Color = Clear

#### Contact Related Features:

- ? Contact Material = Copper Alloy
- ? Contact Mating Area Plating Material = Tin

#### Housing Related Features:

- ? Housing Material = Polycarbonate
- ? Housing Color = Soft White

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- ? Packaging Method = Bulk
- ? Packaging Quantity = 500/Poly Bag

#### Other:

- ? Brand = AMP