



[CONNECTORS](#)

[RF CONNECTORS](#)



✓ Active

TE CONNECTIVITY (TE)

2052 3979 00

Subminiature Coax | SM , SMA

1223136-1

TE Internal Number: 1223136-1

Alias ID: 2052-3979-00

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

**Connector Interface** SMA

**Connector Style** Jack

**Mated Outer Diameter (Approximate)** 6.35 mm [ .25 in ]

**Impedance (Ω)** 50

**Cable Connector Orientation** Straight

[↓ PRODUCT DRAWING](#)  
English

[↓ 3D PDF](#)

## DOCUMENTATION

Product Drawings

### OSM 2 HOLE FLANGE JACK RECEPTACLE-STRAIGHT TERMINAL

PDF (TIFF AVAILABLE)

English

CAD Files

### 3D PDF

PDF

3D

### Customer View Model

2D\_DXF.ZIP

English

## Customer View Model

3D\_IGS.ZIP

English

## Customer View Model

3D\_STP.ZIP

English

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

### Product Type Features

**Connector Interface** SMA

**Connector Style** Jack

### Electrical Characteristics

**Impedance ( $\Omega$ )** 50

### Body Features

**Cable Connector Orientation** Straight

**Body Material** Stainless Steel

**Body Plating Material** Gold

### Contact Features

**Center Contact Plating Material** Gold

**Center Contact Material** Beryllium Copper

**Connector Product Type** Connector Assembly

**RF Connector Contact Configuration** Captivated Contacts

### Mechanical Attachment

**Panel Mount Retention Type** Flange

**Captivation Method** Epoxy

### Dimensions

**Mated Outer Diameter (Approximate)** 6.35 mm [ .25 in ]

**Length** 19.61 mm [ .772 in ]

### Packaging Features

**Packaging Method** Package

### Other

**Dielectric Material** PTFE Fluorocarbon

**Number of Panel Mounting Holes** 2

## PRODUCT COMPLIANCE

Statement of Compliance

**Statement of Compliance**

PDF

---