

1-487769-1 Product Details



1-487769-1

TE Part Number: 1-487769-1

Active

Add to Part List

Flexible Film Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Housing
- 2.54 mm Centerline
- Connector Type = Slimline
- Number of Positions = 13
- Number of Rows = Single

View all Features | Find Similar Products

Live Product Chat

Quick Links

- Check Pricing & Availability
- Search for Tooling
- View Mating Products (12)
- View Contacts (19)
- Product Feature Selector
- Contact Us About This Product
- Request Samples

NEW!

Documentation & Additional Information

Product Drawings:

- HOUSING, RECEPTACLE, DETENT, POLARIZED, FFC (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- Flexible Flat Cable (FFC) Housings with Contact Cavi... (PDF, English)

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version N)
- 3D Model (IGES, Version N)
- 3D Model (STEP, Version N)

List all Documents

Additional Information:

- Product Line Information

Additional Product Images:

- Typical Application

Related Products:

- Tooling
- Mating Products (12)
- Contacts (19)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Housing
- Connector Type = Slimline
- Number of Positions = 13
- Mating Type = Receptacle
- Mating Connector Lock = With
- Mating Connector Lock Type = Detent
- Mating Polarization = Without
- Mounting Ears = Without
- Flame Retardant = Yes

Mechanical Attachment:

- Panel Attachment = Without

Body Related Features:

- Centerline (mm [in]) = 2.54 [0.100]
- Number of Rows = Single

Housing Related Features:

- Housing Material = Thermoplastic
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Terminate To = FFC Cable

Other:

- Brand = AMP