


## 151795 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**151795**

[Active](#)

### Miscellaneous Terminals

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Wire Pin
- ? Insulation Support
- ? Wire Range = 3.00 -6.00<sup>2</sup> [12-10] mm [AWG]
- ? Not For Use With Double Wire
- ? Length = 32.08 mm

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

## Documentation & Additional Information

### Product Drawings:

- ? [TERMINAL, LIPPED BLADE, P.I.D.G., WIRE SIZE: 12 -10 AWG](#) (TIF, English)

### Catalog Pages/Data Sheets:

- ? None Available

### Product Specifications:

- ? None Available

### Application Specifications:

- ? None Available

### Instruction Sheets:

- ? None Available

### CAD Files:

- ? None Available

### Related Products:

- ? [Tooling](#)

[List all Documents](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- ? Product Type = Wire Pin
- ? [Insulation Support](#) = Insulation Support
- ? Color = Blue
- ? Material = Copper
- ? Finish = Tin
- ? Body Style = Straight
- ? Insulation = Yes
- ? Insulation Diameter (mm [in]) = 6.10 [.240] Max.
- ? Proprietary Name = PIDG
- ? Wire/Cable Type = Regular Wire

### Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 3.00 -6.00<sup>2</sup> [12-10]
- ? Double Wire = No
- ? Length (mm [in]) = 32.08 [1.263]
- ? Insulation Sleeve Material = Nylon

### Contact Related Features:

- ? Bulb = Without

### Configuration Related Features:

- ? Diode = Without

### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

### Packaging Related Features:

- ? Packaging Method = Loose Piece

### Other:

- ? Brand = AMP