

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Always EU RoHS/ELV Compliant (Statement of Compliance)

? Receptacle
? Tab Fit = 6.35 x 0.80 mm
? Wire Range = 4.00 - 6.00 ² [11.5 - 10]
mm [AWG]
? Insulation Diameter = 3.70 - 5.20
[.094 - .205] mm [in]
? Receptacle Style = Straight

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

[250 SERIES FASTIN - FASTON RECEPTACLE](#) (PDF, English)

? None Available

? None Available

? None Available

? None Available

? None Available

? Product Line Information

? Tooling

List all Documents

? Product Type = Receptacle
 ? Tab Fit (mm [in]) = 6.35 x 0.80 [.250 x .031]
 ? Insulation Diameter (mm [in]) = 3.70 - 5.20
 [.094 - .205]
 ? Receptacle Style = Straight
 ? Wire/Cable Type = Regular Wire
 ? Finish = Tin
 ? Material = Brass
 ? Insertion Force = Normal
 ? Insulation Support = With
 ? Crimp Type = "F"
 ? FASTON = Yes
 ? CSA Certified = Yes

? Wire Range (mm [AWG]) = 4.00 - 6.00 ² [11.5 - 10]

? UL Rating = Recognized

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Packaging Method = Strip

```
? Line = FASTIN -FASTON .250
? Brand = AMP
```