



+ RELAYS, CONTACTORS & SWITCHES

TACTILE SWITCHES



✓ Active

TE CONNECTIVITY (TE)

## TACT,SMT,SOFT ACTUATOR,T&R

Alcoswitch | Alcoswitch Tactile FSM JX

1571634-2

TE Internal Number: 1571634-2

EU RoHS Compliant

EU ELV Compliant

**Actuator Style** Round

**Operating Function** NO

**Contact Base Material** Stainless Steel

**Contact Plating** Silver

**Dust Proof** No

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

### DOCUMENTATION

Product Drawings

#### **TACTICLE SWITCH 6X6 Mm LOW PROFILE, SURFACE MOUNT W/SOFT BUTTON**

PDF

**English**

CAD Files

**3D PDF**

PDF

**3D**

**Customer View Model**

2D\_DXF.ZIP

**English**

## Customer View Model

3D\_IGS.ZIP

English

## Customer View Model

3D\_STP.ZIP

English

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

### Product Type Features

**Illuminated** With

**Leg Style** Gull Wing

**Actuator Style** Round

**Dust Proof** No

**Product Type** Switch

---

### Configuration Features

**Snap Action** Without

**Tactile** Yes

**Operating Function** NO

**Support Bracket** Without

**Configuration (Pole-Throw)** Single Pole - Single Throw

**Number of Actuators** 1

**Ganged** With

**ESD Grounding Terminal** Without

**Tactile Feel** With

---

### Body Features

**Bushing Style** Unthreaded

**Case Material** PPS

**Actuator Color** Natural

**Actuator Force** 160 g [ 5.648 oz ]

**Case Color** Brown

**Cover Material** Stainless Steel

**Actuator Material** Silicone Rubber

**Actuator Profile** Extended

---

### Contact Features

**Contact Base Material** Stainless Steel

**Contact Plating** Silver

**Contact Current Rating (mA)** 50

---

### Termination Features

**Termination Type** Printed Circuit Board

---

### Mechanical Attachment

**Mounting Type** Surface Mount

**Mounting Angle** With

---

Housing Features

**Low Profile** With

**Process Sealed** No

---

Dimensions

**Switch Height** 5 mm [ .196 in ]

**Actuator Length** 2.4 mm [ .094 in ]

**Button Width (in)** .098

---

Usage Conditions

**Temperature Rating (°C)** Standard

---

Packaging Features

**Packaging Method** Tape & Reel

---

Other

**Comment** (On) indicates momentary position.

---

## PRODUCT COMPLIANCE



Statement of Compliance

**Statement of Compliance**

PDF

---