

1742456-2 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

Ring and Spade Tongue Terminals

RING,10-6,1/4 STUD, TPCU, .469 WIDE

1742456-2

TE Internal Number: 1742456-2

Product Highlights [View All](#)

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Barrel Type = Open Barrel
- Wire/Cable Type = Regular Wire
- Wire Range = 5.00-15.00² [10-6] mm [AWG]

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Receptacle Style	Straight
Barrel Type	Open Barrel
Wire/Cable Type	Regular Wire
Insulation	No
Insulation Support	Non-Insulation Support
Stud Size	1/4 [M6]
Shape	RING-021
Heavy Duty	No
Finish	Tin
Dimensions	
Stud Diameter (mm [in])	6.73 [0.265]
Body Features	
Wire Range (mm [AWG])	5.00-15.00 ² [10-6]
Material	Temp H00 Copper
Stock Thickness (mm [in])	1.27 [0.050]

Contact Features	
Terminal Shape	Ring Tongue
Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
Packaging Features	
Packaging Method	Strip
Other	
Brand	AMP

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)