

Products

Documentation

Resources

My Account

Customer Support

[Home](#) > [Products](#) > [By Type](#) > [D Subminiature](#) > [Product Feature Selector](#) > Product Details

1 - 750877 - 9 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



1 - 750877 - 9

 [Active](#)

.050 Series Cable Connectors (SCSI)

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Hardware
- ? Hardware Type = Wire Lacing Cover
- ? Number of Positions = 100
- ? Wire/Cable Type = Round Jacketed Cable
- ? Wire Range = 0.05 - 0.09 ² [30-28] mm [AWG]

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information	
Product Drawings: ? COVER, TERMINATING, DISCRETE WIRE, AMPLIMITE (PDF, English) Catalog Pages/Data Sheets: ? None Available Product Specifications: ? Connector, AMPLIMITE, Shielded, .050 Series (PDF, English) Application Specifications: ? AMPLIMITE .050 Series Insulation Displacement and Pr... (PDF, English) Instruction Sheets: ? Manual Arbor Frame Assembly 58024 -1 (PDF, English) ? AMP* REPAIR TOOL 58430 -1 FOR AMPLIMITE* .050 -SERIES ... (PDF, English) ? AMPLIMITE .050 Series Connectors (Round -to -Flat Cable) (PDF, English) ? Installation and Use of Mass Termination Tooling (PDF, English) ? Cover Lacing Fixture 91293 -1 for AMPLIMITE .050 Seri... (PDF, English) ? AMP* MANUAL MINIATURE APPLICATOR FRAME ASSEMBLY 91295 -1 (PDF, English) ? Cover Closing Kits and Staple Inserter Kit (PDF, English) ? Tooling Kit 768900 -1 (PDF, English) CAD Files: ? None Available List all Documents	Additional Information: ? Product Line Information Related Products: ? Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Product Type = Hardware ? Number of Positions = 100 ? Wire/Cable Type = Round Jacketed Cable ? Wire Insulation Diameter (mm [in]) = 0.74 - 0.91 [0.029 - 0.036] ? Mating Connector Lock = Without ? Product Series = Series III ? Color = Gray Mechanical Attachment: ? Hardware Type = Wire Lacing Cover Body Related Features: ? Wire Range (mm [AWG]) = 0.05 - 0.09 ² [30-28]	Housing Related Features: ? Housing Material = Thermoplastic ? Housing Flammability Rating = UL 94V -0 Industry Standards: ? RoHS/ELV Compliance = RoHS compliant, ELV compliant ? Lead Free Solder Processes = Not relevant for lead free process ? RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: ? Terminate To = Wire Other: ? Brand = AMP