



**CONNECTORS**

**STANDARD RECTANGULAR CONNECTORS**



✓ Active

TE CONNECTIVITY (TE)

## 1.5 MINI CT LATTICE PLUG/KIT K

AMP MINI-CT | AMP Mini CT Lattice

2-292249-2

TE Internal Number: 2-292249-2

EU RoHS Compliant

EU ELV Compliant

**Product Type** Connector Kit

**UL Flammability Rating** UL 94V-0

**Number of Positions** 26

**Operating Voltage (VAC)** 250

**Operating Temperature Range (°C)** -30 – 105

[↓ PRODUCT DRAWING](#)  
English

[↓ 3D PDF](#)

### DOCUMENTATION

Product Drawings

#### **CABLE CLAMP KIT, HIGH WALL TYPE FOR AMP 1.5mm PITCH MINI CT HYBRID LATTICE CONNECTOR**

PDF (TIFF AVAILABLE)

English

CAD Files

#### **Customer View Model**

3D\_IGS.ZIP

English

#### **Customer View Model**

3D\_STP.ZIP

English

## Customer View Model

2D\_DXF.ZIP

English

## 3D PDF

PDF

English

---

Product Specifications

Product Specification

## AMP Mini Hybrid Lattice Connector, 1.5mm Pitch Lead Free Version

TIF

Japanese

## AMP Mini Hybrid Lattice Connector, 1.5mm Pitch Lead Free Version

PDF

Japanese

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

Product Type Features

**Kit Type** Cable Clamp Kit

**Product Type** Connector Kit

---

Configuration Features

**Number of Positions** 26

**Keying** A

---

Electrical Characteristics

**Operating Voltage (VAC)** 250

---

Body Features

**Color** Gray

**Cable Clamp Material** Steel

**Cable Clamp Plating Material** Zinc

---

Mechanical Attachment

**Screw Material** Steel

**Screw Plating Material** Zinc

---

Usage Conditions

**Operating Temperature Range (°C)** -30 – 105

---

Industry Standards

**UL Flammability Rating** UL 94V-0

---

Packaging Features

**Packaging Quantity** 120

**Packaging Method** Box

---

**PRODUCT COMPLIANCE**



Statement of Compliance

**Statement of Compliance**

PDF

---